

1MP IR Bullet HD Camera

- . 1/4" 1.0MP CMOS Sensor
- . AHD/CVI/TVI/CVBS 4 IN 1
- . 3.6mm Fixed Lens
- . IR Distance max 30m
- . IP66 outdoor, OSD&UTC support



SPECIFICATION	
Model NO.	DFR31
Video Output Mode	AHD/CVI/TVI/CVBS 4 IN 1
Camera	
Image Sensor	1/4" 1.0MP CMOS Sensor
Image Resolution	1MP 720P/ 960H
Effective Pixels	1280*720
TV System	PAL/NTSC
Electronic Shutter	1/25s~1/50,000s , 1/30s~1/60,000s
S/N Ratio	≥50dB
Scanning System	Progressive Scan
Lens	
Focus Length	3.6mm (6mm Optional)
Focus Control	Fixed
Lens Type	Fixed
Pixels	2M Pixels
Auto Iris Support	NO
Night Vision	
Infrared LED	42μ x 2PCS
Infrared Distance	30M

IR Status	Under 10 Lux by CDS
IR Power On	CDS Auto Control
Camera Features	
Starlight	/
Day/Night	YES
OSD Menu Language	YES
White Balance	AUTO / MANUAL
Gain Control	AUTO
Noise Reduction	DNR
Picture Adjustment	YES
WDR	YES
OSD Support	YES
UTC	YES
Dip Switch	Optional
General	
Housing	Metal, IP66
Bracket	YES
Dual Voltage	NO
IR Cut Filter	YES
Heater	NO
Audio	Optional
Operation Temperature	-10°C ~ +50°C RH95% Max
Storage Temperature	-20°C ~ +60°C RH95% Max
Power Source	DC12V±10%, 600mA
Dimension	157(W) x 70(H) x 66(D)mm
Weight	650g