



## Proinstall-200-D



## Product Overview

**Combined installation meter like ProInstall-100 and also offers:**

- Testing of all-current sensitive RCD / FI (Type B)
- Memory for approx. 1000 measurements
- Grounding measurement (optional with probes)
- RCD / FI analysis to check all parameters of an RCD / FI

## Features

- Loop resistance measurement
- Mains internal resistance measurement
- Short circuit current measurement
- Low impedance and continuity measurement
- insulation measurement
- RCD / FI measurement (contact voltage, tripping time, tripping current - rising current)
- Voltage and frequency measurement

## device information

- Memory for approx. 400 measurements with 3 levels for assigning distributor and circuit numbers
- IR / USB interface to transfer the stored measured values to the PC
- Software for logging optionally available for printing a test report
- Integrated socket test with touch electrode for incorrectly connected sockets or missing protective conductor
- Easy-to-read, large LC-display with background lighting and a particularly large viewing angle
- Auto Power Off

## Product highlights

- Compact and robust design allows working even under the most difficult conditions (weighs only 1500g)
- Easy-to-use, intuitive user interface allows you to work immediately and efficiently
- Probe with test button included
- Loop resistance measurement and short circuit current measurement without triggering the RCD / FI