



Datenblatt - Fiche technique - Data sheet


**11.04.5564**



ROLINE GOLD HDMI High Speed Kabel, ST-ST, 20,0m


ROLINE GOLD Câble HDMI High Speed, M-M, 20 m

ROLINE GOLD HDMI High Speed Cable, M/M, 20 m



**Electrical Test:**

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 5 ohm max.
3. Insulation Resistance: 10M ohm min.
4. Hi-pot:300V DC/10ms



11	Wire Clip OD:10.0mm	2	pcs
10	TUBE BLACK #1.5mm THIN	0.032	m
9	HDMI 20# BALCK ABS JACKET	2	pcs
8	HDMI M TRANSPARENT DUST COVER	2	pcs
7	45P BLACK PVC	16	g
6	TRANSPARENT PE	3	g
5	TUBE BALCK #0.8mm THIN.	0.024	m
4	TUBE BALCK #2.0mm THIN.	0.08	m
3	HDMI 20# Shell aluminium alloy laser etching HDMI LOGO	2	pcs
2	HDMI M SOLDER TYPE,GOLD PLATED SHELL, BLACK INSULATION	2	pcs
1	UL20276 (24AWG*1P+EAM)*5C+24AWG*4C+MAEB(50%AL) OD:10.0mm WITH BLACK/YELLOW NET	20	M
NO.	DESCRIPTION	Q'TY	UNIT

	TOLERANCE				rotronic
		INCHES	M/M		
	.X	.015	.30		
.XX	.010	.10			
.XXX	.005	.05			
DRAWN BY				11.04.5564	
CHECK BY				ROLINE GOLD HDMI Cable, A M / A M 20m, black w/yellow & black nylon net	
APPD BY				SCALE	NONE
				UNIT	MM
				DATE	2013.07.26
				DRAWING NO.:	REV. A
					1/1