



Datenblatt - Fiche technique - Data sheet

11.04.5646



ROLINE GOLD DisplayPort Kabel, DP ST - ST, 3,0m

ROLINE GOLD Câble DisplayPort DP M - DP M, 3,0m


ROLINE GOLD DisplayPort Cable, DP-DP, M/M, 3 m

ROHS-COMPLIANT

LTR	REV	DESCRIPTION	DATE

DISPLAYPORT MALE
INS:BLACK

DISPLAYPORT MALE
INS:BLACK



NOTE:

- CABLE: UL-20276 [#30(7/0.1 T.C)×1P INS:FOAM-PE+D.W(7/0.1 T.C)+AL/MY +Hot-melt Mylar]×5C + #30(7/0.1 T.C)×4C INS:Polyethylene+AL/MY+ B.D(85%) PVC JACKET, OD:6.5±0.2mm COLOR:MATT BLACK(INK-K01).
- CONNECTOR:
P1 & P2: DISPLAYPORT 20P MALE W/PCB & LATCH CONTACT:15U"
GOLD PLATED SHELL.
- SHIELD:INNER MOLD MUST BE WRAPPED COPPER TO CONNECTOR SHELL & CABLE BRAID
- HOOD:ASS'Y TYPE, PLASTIC HOOD COLOR: GOLD
- ELECTRICAL TEST:
(1)100% OPEN SHORT & MIS WIRE TEST.
(2)CONTACT RESISTANCE 3 ohm Max.
(3)INSULATION RESISTANCE 10M ohm Min.
- PACKING: EACH PC / POLYBAG+BIG HEADER CARD+BAR CODE LABEL.

200-1484-3	11.04.5647-5	5000	50	5	10
200-1484-2	11.04.5646-10	3000	30	10	20
200-1484-1	11.04.5645-10	2000	30	10	20
DWG	P/N	L(mm)	T(mm)	PCS/INNER CARTON	PCS/CARTON

Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05

Rotronic co., LTD.
Title
DISPLAYPORT ASS'Y CABLE

Draw
FANNIE 12/13/10'

Customer P/N

Check

App'd
Customer: T-RAG

Engr

Scale| NONE | Units | M/M | Third Angle Projection
Dwg No. 200-1484 | REV:A | Sheet: 1/2

LTR	REV	DESCRIPTION	DATE

PIN OUT

P1	P2	CABLE FUNCTION
1	12	ML_Lane 0(p)
3	10	ML_Lane 0(n)
2	11	GND
4	9	ML_Lane 1(p)
6	7	ML_Lane 1(n)
5	8	GND
7	6	ML_Lane 2(p)
9	4	ML_Lane 2(n)
8	5	GND
10	3	ML_Lane 3(p)
12	1	ML_Lane 3(n)
11	2	GND
15	15	AUX CH(p)
17	17	AUX CH(n)
16	16	GND
13	13	CONFIG1
14	14	CONFIG2
18	18	Hot Plug Detect
19	19	Return DP_PWR
SHELL	SHELL	

B.D

Tolerance Inch M/M		Title	
X	.015 .30	Rotronic co., LTD.	
XX	.010 .10	DISPLAYPORT ASS'Y CABLE	
XXX	.005 .05	Customer P/N	
Draw	FANNIE 12/13/10'	Customer: T-RAG	
Check	Engr	App'd	Scale NONE
			Units M/M
			Third Angle Projection
		Dwg No. 200-1484	REV: A
			Sheet: 2/2