



Datenblatt - Fiche technique - Data sheet


11.09.4269



ROLINE GOLD S-Video Kabel, Stecker / Stecker, 10,0m

ROLINE GOLD Câble S-Vidéo, M / M, 10,0m

ROLINE GOLD S-Video Cable, Male / Male, 10.0m



PIN OUT

P1		P2
1	— BLACK	1
3	— SPRIAL	3
2	— RED	2
4	— SPRIAL	4

Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 5 ohm Max
3. Insulation Resistance: 10M ohm Min
4. Hi-Pot: 100V DC/10ms

REV.	DESCRIPTION	DATE
1	ROTRONIC Co., Ltd.	
TOLERANCE INCHES M/M		ROLINE Gold S-Video Cable M-M, 10m
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05
DRAWN BY	JOE	CUSTOMER : 11.09.4269
CHECK BY		CUSTOMER P/N :
APPD BY		SCALE NONE
		UNIT MM
		DATE 2012.10.08
		DRAWING NO:
		REV A
		1/2

QTY	UNIT	DESCRIPTION
2	SET	MINI DIN 4P M copper shell ,PIN TIN PLATED,SHELL GOLD PLATED,INSULATION:white(PLATED 24K GOLD)
L	M	UL2919 1354(S)(28AWG 7/0.12TA+S(30/0.10TC)+ MY)*2C 75oh OD:5.0MM BLACK + black/gold nylon
Q'TY	UNIT	DESCRIPTION