



Datenblatt - Fiche technique - Data sheet


11.02.8869




ROLINE USB 3.0 Kabel, Typ A-B, 0,8m

ROLINE Câble USB 3.0 Type A-B, 0.8m

ROLINE USB 3.0 Cable, A - B, M/M, 0.8 m



WIRE ADDRESS



- Electrical Test:
1. 100% TEST OPEN SHORT MIS-WIRE.
 2. CONTACT RESISTANCE:3Ω MAX.
 3. INSULATION RESISTANCE:5MΩ MIN.
 4. HI-POT:300V DC/10MS.

4	45P PVC BLACK		6
3	USB 3.0 B MALE(Blue Insulator, Shell Nickel Plated, Pin Gold Plated 30U ^m)	1	PCS
2	USB 3.0 A MALE(Blue Insulator, Shell Nickel Plated, Pin Gold Plated 30U ^m)	1	PCS
1	UL2725 OR UL20276 (28AWG*1P+EAM)*2C+28AWG*1P+24AWG*2C+AEB, OD=5.5mm, BLACK PVC JACKET (BC Wire)	1	PCS
PRODUCT SPECIFICATIONS		Quantity	Unit
NUMBER	1	2	4

VER.A	REVISE	DATE
D		
C		
B		

item no. : 11.02.8869

Draw Sam Date: 2014.12.05

Approval F16

Duty F16



Sample NO.

Drawings of 1:1 Proportion: 100mm A4