



| | | |
|--|--------------------------------|---|
| P0: | Cello Electronics (UK) Ltd. |  |
| | Product Photo |  |
| General Feature | Customer Model No.(Brand) | C32227FT2 |
| | Panel(60Hz/120Hz/3D) | ST3151A06-1(60Hz) |
| | Destination Country | UK&EU |
| | Safety and Regulation | CE,ROHS |
| | Panel System | 31.5 inch LED Panel(Approx. 74cm) |
| | Purpose | TV/Monitor Optional |
| | Aspect Ratio | 16:9 |
| | Max. Resolution | 1366 x 768 |
| | Contrast Ratio (Typical) | 3000:1(TYP) by panel |
| | Brightness(TYP cd/m2) | 250nits(TYP) by panel |
| | Display Area(mm) | 697.68 (H) x 392.256 (V) |
| | Pixel Pitch (mm) | 0.17025 (H) x 0.51075 (V) |
| | Display Colors | 16.7M |
| | Viewing Angle(L/R/U/D) | 89/89/89/89(CR≥10) |
| | HD Supported Definitions | 1080i/720P/576P/480P |
| | Response Time(Tr+Tf /typ.) | 6.5ms |
| | AC Switch | N/A |
| | Cabinet Color | Plano Black |
| Tilt Angle (up and down movement) | N/A | |
| Swivel Angle (left and right movement) | N/A | |
| Wall Mounting Support(Screw Size) | VESA,200 x 100mm(M4 x 8) | |
| Reception | TV Solution | Mstar3463 |
| | TV System | ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4 |
| | TV Band | ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz) |
| | 5V from Antenna | N/A |
| | NTSC Playback | N/A |
| | Digital Comb Filter | 3D |
| | De-interlace Image Enhancement | N/A |
| | Tuning System | FST |
| | Clock / Time Display | N/A |
| | CI PLUS | N/A |
| Number of channel for storing | 100 Analog / 400 Digital | |
| Sound | Bass | YES |
| | Treble | YES |
| | Balance | YES |
| | Sound Mode | Standard / Music /Movie / Sports /User |
| | Stereo System | NICAM/A2 |
| | Audio Output | 2*6W |
| | Dolby | YES |
| | SRS | N/A |
| Connectors Jack | RF Antenna | 1 |
| | HDMI | YES*3 |
| | CVBS | YES*1 |
| | PC In | D-sub 15Pin x 1 |

| | | |
|----------------|---|--|
| | Audio In | PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1 |
| | Scart | YES× 1 |
| | YPbPr | YES× 1 |
| | Digital Audio Out | YES× 1 |
| | Earphone Out | YESx 1(3.5 φ Mini Jack) |
| | USB | YESx 1(Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png) |
| | CI | YES× 1 |
| | RCA | N/A |
| DVD | DVD Loader | FORYOU |
| | DVD Solution | MTK-MTK1389 |
| | DVD/DVD-R/DVD+R/DVD-RW/DVD+RW/CD/MP3/JPEG playback | YES |
| | DVD Reverse Play | YES |
| | Skip Forward/Reverse | YES |
| | DVD Multi-Speed Scan/Slow | YES |
| | Slot-Load Type Vertical Play DVD Mechanism | YES |
| | DIV X | \ |
| Other Features | APS | ATV, DVBT, DVBC storage in capture order. |
| | OSD Language | English / French / German / Italian/Spanish/Portuguese |
| | Teletext | 1000pages |
| | EPG (Electronic Program Guide) | 7 days (not 7 days from satellite transmissions) |
| | Automatic Tuning | YES |
| | Sleep Timer | YES(240min) |
| | Noise Reduction | YES |
| | Color Temperature Adjustment | YES |
| | Picture Mode | Standard /Dynamkic/Mild /User |
| | Home Mode | YES |
| | Sleep Mode | YES |
| | Hotel Mode | YES |
| Power | Power Supply | AC 100V-240V~ 50Hz/60Hz |
| | Operation Power Consumption | 34W |
| | Max power Consumption | <60W |
| | Standby Power Consumption | 0.4W |
| | Energy Efficiency Class | A |
| Accessories | USER'S Manual | ENGLISH |
| | Remote Control | YES× 1 |
| | Power Cable | YES× 1 |
| | Adapter | N/A |
| | Adapter Cables | N/A |
| | Warranty | YES |
| | Battery | 1.5V(AAA)×2 |
| Dimension | Unit Dimension With Stand (W x D x H mm) | 738*190*488 |
| | Unit Dimension Without Stand (W x D x H mm) | 738*76*446 |
| | Weight of unit(kg) | 6.5 |
| | Carton Dimension Without Stand Assembled(W x H x D mm) | / |
| | Weight of gift box with content(kg) | |
| | Weight of carton/paper(Kg) | / |
| | Weight of styrofoam(Kg) | / |