



P0:	Cello Electronics (UK) Ltd.	
	Product Photo	
General Feature	Customer Model No.(Brand)	C50238DVB T2-LED
	Panel(60Hz/120Hz/3D)	V500HJ3-PE1
	Destination Country	UK&EU
	Safety and Regulation	CE,ROHS
	Panel System	50 inch LED Panel(Approx. 127cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1920 x 1080
	Contrast Ratio (Typical)	4000:1(TYP) by panel
	Brightness(TYP cd/m2)	250nits(TYP) by panel
	Display Area(mm)	1095.84(H) x 616.41(V)
	Pixel Pitch (mm)	0.1903(H) x 0.5708(V)
	Display Colors	16.7M
	Viewing Angle( L/R/U/D )	89/89/89/89(CR≥10)
	HD Supported Definitions	1080p/1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	9.5ms
	AC Switch	N/A
	Cabinet Color	plano black
	Tilt Angle (up and down movement)	N/A
Swivel Angle (left and right movement)	N/A	
Wall Mounting Support(Screw Size)	VESA, 200 x 200mm (M6 x 10 2pcs/ M6 x 16 2pcs )	
Reception	TV Solution	Mstar3463
	TV System	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVB T2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Digital Comb Filter	3D
	De-interlace Image Enhancement	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	CI PLUS	N/A
	Number of channel for storing	100 Analog / 400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*6W
	Dolby	N/A
	SRS	N/A
Connectors Jack	RF Antenna	1
	HDMI	YES*3
	CVBS	YES*1
	PC In	D-sub 15Pin x 1

	<b>Audio In</b>	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1
	<b>Scart</b>	YES× 1
	<b>YPbPr</b>	YES× 1
	<b>Coax</b>	YES× 1
	<b>Earphone Out</b>	YESx 1(3.5 φ Mini Jack)
	<b>USB</b>	YESx 1( Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	<b>CI</b>	YES× 1
	<b>RCA</b>	N/A
Other Features	<b>APS</b>	ATV, DVBT, DVBC storage in capture order.
	<b>OSD Language</b>	English / French / German / Italian/Spanish/Portuquese
	<b>Teletext</b>	1000pages
	<b>EPG (Electronic Program Guide)</b>	7 days (not 7 days from satellite transmissions)
	<b>Automatic Tuning</b>	YES
	<b>Sleep Timer</b>	YES(240min)
	<b>Noise Reduction</b>	YES
	<b>Color Temperature Adjustment</b>	YES
	<b>Picture Mode</b>	Standard /Dynamkic/Mild /User
	<b>Home Mode</b>	YES
Power	<b>Power Supply</b>	AC 100V-240V~ 50Hz/60Hz
	<b>Operation Power Consumption</b>	85W
	<b>Max power Consumption</b>	<120W
	<b>Standby Power Consumption</b>	0.4W
	<b>Energy Efficiency Class</b>	A
Accessories	<b>USER'S Manual</b>	ENGLISH
	<b>Remote Control</b>	YES× 1
	<b>Power Cable</b>	YES× 1
	<b>Adapter</b>	N/A
	<b>Adapter Cables</b>	N/A
	<b>Warranty</b>	YES
	<b>Battery</b>	1.5V(AAA)×2
Dimension	<b>Unit Dimension With Stand (W x D x H mm)</b>	1132 x 260 x 720 mm
	<b>Unit Dimension Without Stand (W x D x H mm)</b>	1132 x 86 x 655 mm
	<b>Weight of unit(kg)</b>	9.8
	<b>Weight of gift box with content(kg)</b>	/
	<b>Dimensions of mastercarton (W x H x D mm)</b>	/
	<b>Weight of carton/paper(Kg)</b>	/
	<b>Weight of styrofoam(Kg)</b>	/