



P0:	Cello Electronics (UK) Ltd.	
	Product Photo	
General Feature	Customer Model No.(Brand)	C75ANSMT-4K
	Panel(60Hz/120Hz/3D)	V750DK1-QS5
	Destination Country	UK&EU
	Safety and Regulation	CE,ROHS
	Panel System	75 inch LED Panel(Approx. 190cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	3840 x 2160
	Contrast Ratio (Typical)	4000:1(TYP) by panel
	Brightness(TYP cd/m2)	200nits(TYP) by panel
	Display Area(mm)	1650.24(H) x 928.26 (V)
	Pixel Pitch (mm)	0.143(H) x 0.43(V)
	Display Colors	1.07G
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	HD Supported Definitions	3840x2160/1080p/1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	6.5ms
	AC Switch	N/A
	Cabinet Color	Silver
Tilt Angle (up and down movement)	N/A	
Swivel Angle (left and right movement)	N/A	
Wall Mounting Support(Screw Size)	VESA,400 x 200mm (M10 *18)	
Reception	TV Solution	Mstar3458 +Mstar9280
	TV System	DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Digital Comb Filter	3D
	De-interlace Image Enhancement	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	CI PLUS	N/A
Number of channel for storing	100 Analog / 400 Digital	
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*6W
	Dolby	N/A
SRS	N/A	
Connectors Jack	RF Antenna	1
	HDMI	YES*3(ver2.0)
	CVBS	YES*1
	PC In	N/A
	Audio In	N/A
	Scart	N/A

	YPbPr	N/A
	Digital Audio out	YES× 1
	Earphone Out	N/A
	USB on TV	YES× 1(Multi Media Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	N/A
	RCA	YES× 1
	RJ45 on Android	YES× 1
	Mirco SD card on Android	YES× 1
	USB on Android	YES× 2(Multi Media & Wireless Mouse and Keyboard)
Other Features	APS	DVBT, DVBC storage in capture order.
	OSD Language	English / French / German / Italian/Spanish/Portuquese
	Teletext	N/A
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard /Dynamkic/Mild /User
	Home Mode	YES
	Wifi on Android	YES
	Hotel Mode	YES
Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	172W
	Max power Consumption	<300W
	Standby Power Consumption	0.4W
	Energy Efficiency Class	A
Accessories	USER'S Manual	N/A
	Remote Control	YES× 1
	Power Cable	YES× 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES
	Battery	1.5V(AAA)×2
Dimension	Unit Dimension With Stand (W x H x D mm)	1684 x 295 x 1051 mm
	Unit Dimension Without Stand (W x H x D mm)	1684x 95 x 976 mm
	Weight of unit(kg)	28
	Weight of gift box with content(kg)	
	Dimensions of mastercarton (W x H x D mm)	/
	Weight of carton/paper(Kg)	/
	Weight of styrofoam(Kg)	/