


P0:	Cello Electronics (UK) Ltd.	
		C43227T2
	EAN	5060062267051
General Feature	Customer Model No.(Brand)	C43227T2
	Panel(60Hz/120Hz/3D)	HV430FHB(60Hz)
	Destination Country	UK&EU
	Safety and Regulation	CE,ROHS
	Panel System	43 inch LED Panel(Approx. 109cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1920x1080
	Contrast Ratio (Typical)	4000:1(TYP) by panel
	Brightness(TYP cd/m2)	230nits(TYP) by panel
	Display Area(mm)	940.896 (H) x 59.254 (V)
	Pixel Pitch (mm)	0.4902(H) x 0.4902(W)
	Display Colors	16.7M
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	HD Supported Definitions	1080p/1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	8ms
	AC Switch	N/A
	Cabinet Color	piano black
	Tilt Angle (up and down movement)	N/A
	Swivel Angle (left and right movement)	N/A
Wall Mounting Support(Screw Size)	VESA, 200 x 200mm(M5 x 10)	
Reception	TV Solution	Mstar3463
	TV System	ATV: PAL BG/DK/ SECAM BG/DK/LL' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Digital Comb Filter	3D
	De-interlace Image Enhancement	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	CI PLUS	N/A
Number of channel for storing	100 Analog / 400 Digital	
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*8W
	Dolby	N/A
	SRS	N/A
Connectors Jack	RF Antenna	1
	HDMI	YES*3
	CVBS	YES*1
	PC In	D-sub 15Pin x 1
	Audio In	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1
	Scart	YES* 1

	YPbPr	YES* 1
	Digital Audio Out	YES* 1
	Earphone Out	YESx 1(3.5 φ Mini Jack)
	USB	YESx 1(Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	YES* 1
	RCA	N/A
Other Features	APS	ATV, DVBT, DVBC storage in capture order.
	OSD Language	English / French / German / Italian/Spanish/Portuguese
	Teletext	1000pages
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard /Dynamkic/Mild /User
	Home Mode	YES
	Sleep Mode	YES
	Hotel Mode	YES
	Power	Power Supply
Operation Power Consumption		54W
Max power Consumption		<120W
Standby Power Consumption		0.4W
Energy Efficiency Class		A+
Accessories	USER'S Manual	ENGLISH
	Remote Control	YES* 1
	Power Cable	YES* 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES
	Battery	1.5V(AAA)*2
Dimension	Unit Dimension With Stand (W x H x D mm)	969*612*257mm
	Unit Dimension Without Stand (W x H x D mm)	969*564*86 mm
	Weight of unit(kg)	7.7Kg
	Dimensions of Gift Box (W x H x D mm)	1080x664x150
	Weight of Gift Box with content(Kg)	10.16
	Weight of carton/paper(Kg)	/
	Weight of styrofoam(Kg)	/

ATTN: the panels parameters listed in the spec are only for reference .

COPY

C43227T2

A bigger screen must be better and this Cello TV with Freeview HD Channels and a large 43" Full HD 1080P screen is attractively priced and richly featured. Ideal for the sitting room or larger bedroom this TV is easy to set up and operate. In addition to Freeview HD this TV has 3 x HDMI inputs for connecting media boxes and games consoles for glorious Full HD viewing. A USB port enables the recording of live TV to your USB device or play media files saved from your PC.