


P0:	Cello Electronics (UK) Ltd.	
		C43227FT2
	EAN	5060062267068
General Feature	Customer Model No.(Brand)	C43227FT2
	Panel(60Hz/120Hz/3D)	HV430FHB(60Hz)
	Destination Country	UK&EU
	Safety and Regulation	CE,ROHS
	Panel System	43 inch LED Panel(Approx. 109cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1920x1080
	Contrast Ratio (Typical)	4000:1(TYP) by panel
	Brightness(TYP cd/m2)	230nits(TYP) by panel
	Display Area(mm)	940.896 (H) x 59.254 (V)
	Pixel Pitch (mm)	0.4902(H) x 0.4902(W)
	Display Colors	16.7M
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	HD Supported Definitions	1080p/1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	8ms
	AC Switch	N/A
	Cabinet Color	piano black
	Tilt Angle (up and down movement)	N/A
	Swivel Angle (left and right movement)	N/A
Wall Mounting Support(Screw Size)	VESA, 200 x 200mm(M5 X10)	
Reception	TV Solution	Mstar3463
	TV System	ATV: PAL BG/DK/ SECAM BG/DK/LL' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Digital Comb Filter	3D
	De-interlace Image Enhancement	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	CI PLUS	N/A
Number of channel for storing	100 Analog / 400 Digital	
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*8W
	Dolby	N/A
	SRS	N/A
Connectors Jack	RF Antenna	1
	HDMI	YES*3
	CVBS	YES*1
	PC In	D-sub 15Pin x 1
	Audio In	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1
	Scart	YES* 1

	YPbPr	YES× 1
	Digital Audio Out	YES× 1
	Earphone Out	YES× 1(3.5 φ Mini Jack)
	USB	YES× 1(Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	YES× 1
	RCA	N/A
DVD	DVD Loader	FORYOU
	DVD Solution	MTK-MTK1389
	DVD/DVD-R/DVD+R/DVD-RW/DVD+RW/CD/MP3/JPEG playback	YES
	DVD Reverse Play	YES
	Skip Forward/Reverse	YES
	DVD Multi-Speed Scan/Slow	YES
	Slot-Load Type Vertical Play DVD Mechanism	YES
	DIV X	\
Other Features	APS	ATV, DVBT, DVBC storage in capture order.
	OSD Language	English / French / German / Italian/Spanish/Portuguese
	Teletext	1000pages
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard /Dynamic/Mild /User
	Home Mode	YES
	Sleep Mode	YES
	Hotel Mode	YES
Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	54W
	Max power Consumption	<120W
	Standby Power Consumption	0.4W
	Energy Efficiency Class	A+
Accessories	USER'S Manual	ENGLISH
	Remote Control	YES× 1
	Power Cable	YES× 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES
	Battery	1.5V(AAA)×2
Dimension	Unit Dimension With Stand (W x H x D mm)	969*612*257mm
	Unit Dimension Without Stand (W x H x D mm)	969*564*93 mm
	Weight of unit(kg)	8.2Kg
	Dimensions of Gift Box (W x H x D mm)	1080x664x150
	Weight of Gift Box with content(Kg)	10.5Kg
	Weight of carton/paper(Kg)	1.64
	Weight of styrofoam(Kg)	0.58

ATTN: the panels parameters listed in the spec are only for reference .

COPY

C43227FT2

A versatile item for any avid viewer this Full HD 43" TV with Freeview HD Channels ensures a stunning viewing experience. Incorporating a DVD Player this neat large screen TV operates from 1 remote control and is easy to set up and operate. With a USB port for recording live TV or playing media files from your memory device and 3 x HDMI inputs for consoles and media boxes you'll always have something to watch. This TV/DVD Combi makes a bold statement and is versatile enough for viewers of all types and ages.