



P0:	Cello Electronics (UK) Ltd.	
	Product Photo	
General Feature	Customer Model No.(Brand)	C22277T2 S2 CP6
	Panel(60Hz/120Hz/3D)	T215HTN01.1 (60Hz)
	Destination Country	UK
	Safety and Regulation	CE
	Panel System	21.6 inch LED Panel(Approx. 55cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1920X1080
	Contrast Ratio (Typical)	600:1(TYP) by panel
	Brightness(TYP cd/m2)	200nits(TYP) by panel
	Display Area(mm)	479.0x270.0
	Pixel Pitch (mm)	0.24825 (H) x 0.24825(V)
	Display Colors	16.7M
	Viewing Angle(H/V)	89/89/89/89(CR≥5)
	HD Supported Definitions	1080p/1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	18ms
	Switch	YES
	Cabinet Color	Piano Black
	Wall Mounting Support(Screw Size)	VESA, 100 x 100mm(M4x 8)
Reception	TV Solution	Mstar3463
	TV System	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV-DVB-T & DVB-C & DVB-S2&DVBT2, MPEG 2,MP@ML, MPEG 4 & H.265
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz) DVB-S2 (950MHz-- 2150MHz)
	5V from Antenna	YES
	Digital Comb Filter	3D
	Tuning System	FST
	CI PLUS	YES
	Number of channel for storing	100 Analog / 400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*2W
Connectors Jack	RF Antenna	2
	HDMI	YES*1(ver1.4)
	CVBS	YES*1(Mini)
	PC In	YES x1
	Audio In	YES x1
	Earphone Out	YES x1
	USB	YESx 4(2 for Multi Media and PVR 2 for USB Charging)
	CI	YES* 1

	DC 12V out	YES× 2
	Built In Battery Charging Indicator	YES× 1(It is on during charging, it flashes when full)
Other Features	APS	ATV, DVBT, DVBC storage in capture order. DVBS2 pre-set list.
	OSD Language	English / French / German / Italian/Spanish/Portuguese
	Teletext	1000pages
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Smart Backlight setting	Auto set related with the power supply.
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard /Dynamkic/Mild /User
	Hotel Mode	YES
	Power	Power Supply
6-10Hours Consumption		7.5W
4-6Hours Consumption		10W
Daytime Consumption		15W
Standby Power Consumption		0.4W
Accessories	USER'S Manual	ENGLISH
	Quick Start Guide	YES× 1
	Remote Control	YES× 1
	Adapter Cables	N/A
	Warranty	YES
	Adapter	YES× 1(DC 19V-3.16A/AC 100V-240V~ 50Hz/60Hz)
	Car Adapter	YES x 1(DC 12-24V in & 19V-2.5A out)
	Lamp	YES× 2
	Lamp Cable	YES× 2
	Antenna	YES x1 (For Air Tuning)
	Battery for remote	1.5V(AAA)×2
Dimension	Unit Dimension With Stand (W x H x D mm)	509 x 165 x 341
	Unit Dimension Without Stand (W x H x D mm)	509 x 86 x 307
	Weight of unit(kg)	2.95

ATTN: the panels parameters listed in the spec are only for reference .

the weight of the battery is 693g

the battery is not Lithium Ion or Polymer

Battery type : LiFeP04