

	Cello Electronics (UK) Ltd.	
	EAN	5060062267396
General Feature	Model No.	C22230T2
	Panel(60Hz/120Hz/3D)	M215HTN01.1
	Destination Country	UK
	Safety and Regulation	CE
	Panel System	21.5 inch LED Panel(Approx. 55cm)
	Max. Resolution	1920 x 1080
	Contrast Ratio (Typical)	600:1
	Brightness(TYP cd/m2)	180
	Display Colors	16.7M
	Viewing Angle(L/R/U/D)	85/85/80/80(CR ≥ 10)
	HD Supported Definitions	1080p/1080i/720P/576P/480P
	AC Switch	N/A
	Cabinet Color	Piano Black
	Wall Mounting Support(Screw Size)	200 x 100mm(M4 x 8)
Reception	TV Solution	Mstar3663
	TV System	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVB-T2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	Number of channel for storing	100 Analog / 400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2 x 3W
	Speaker Frequency range	150-20K Hz
	Speaker Distortion	<=7% Max
	Speaker Impedance	4ohm
Connectors Jack	RF Antenna	1
	HDMI	YES x 1
	CVBS	YES x 1
	PC In	YES x 1
	Audio In	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1(Mini Jack ,Shared with Ypbpr)
	Scart	N/A
	YPbPr	YES x 1(3.5 φ Mini Jack)
	Digital Audio out	YESx 1
	Earphone Out	YESx 1
	USB on TV	YESx 1
	CI	YESx 1
Other Features	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Norge, Dansk, Svenska, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamic / Mild / User
Home Mode	YES	

	Wifi on Android	N/A
	Hotel Mode	YES
Power	Power Supply	DC12V-3A /AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	21W
	KWh/annum	31kWh
	Max power Consumption	36W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A
	Accessories	USER'S Manual
Remote Control		YES x 1
Power Cable		N/A
Adapter		YES x 1
Adapter Cables		N/A
Warranty		YES x 1
Battery		1.5V(AAA)x2
Dimension	Unit Dimension With Stand (W x D x H mm)	504 x 160 x 342
	Unit Dimension Without Stand (W x D x H mm)	504 x 79 x 306
	Weight of unit(kg)	2.2
	Gift Box Dimension(W x H x Dmm)	
	Weight of gift box with content(kg)	
	Weight of carton/paper(Kg)	
	Weight of styrofoam(Kg)	