


	<b>Cello Electronics (UK) Ltd.</b>	
	<b>Product Photo</b>	
	<b>EAN</b>	<b>5060062267150</b>
<b>General Feature</b>	<b>Model No.</b>	C20230T2
	<b>Panel(60Hz/120Hz/3D)</b>	M195XTN01
	<b>Destination Country</b>	UK
	<b>Safety and Regulation</b>	CE
	<b>Panel System</b>	19.5 inch LED Panel(Approx. 49.5cm)
	<b>Max. Resolution</b>	1366 x 768
	<b>Contrast Ratio (Typical)</b>	600:1
	<b>Brightness(TYP cd/m2)</b>	180
	<b>Display Colors</b>	16.7M
	<b>Viewing Angle( L/R/U/D )</b>	45/45/20/45(CR ≥ 10)
	<b>HD Supported Definitions</b>	1080i/720P/576P/480P
	<b>AC Switch</b>	N/A
	<b>Cabinet Color</b>	Piano Black
<b>Wall Mounting Support(Screw Size)</b>	100 x 100mm( M4 x 8 )	
<b>Reception</b>	<b>TV Solution</b>	Mstar3663
	<b>TV System</b>	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	<b>TV Band</b>	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	<b>5V from Antenna</b>	N/A
	<b>Tuning System</b>	FST
	<b>Clock / Time Display</b>	N/A
	<b>Number of channel for storing</b>	100 Analog / 400 Digital
<b>Sound</b>	<b>Bass</b>	YES
	<b>Treble</b>	YES
	<b>Balance</b>	YES
	<b>Sound Mode</b>	Standard / Music /Movie / Sports /User
	<b>Stereo System</b>	NICAM/A2
	<b>Audio Output</b>	2 x 3W
	<b>Speaker Frequency range</b>	150-20K Hz
	<b>Speaker Distortion</b>	<=7% Max
	<b>Speaker Impedance</b>	4ohm
<b>Connectors Jack</b>	<b>RF Antenna</b>	1
	<b>HDMI</b>	YES x 1
	<b>CVBS</b>	YES x 1
	<b>PC In</b>	YES x 1
	<b>Audio In</b>	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1(Mini Jack ,Shared with Ypbpr)
	<b>Scart</b>	N/A
	<b>YPbPr</b>	YES x 1(3.5 φ Mini Jack)
	<b>Digital Audio out</b>	YESx 1
	<b>Earphone Out</b>	YESx 1
	<b>USB on TV</b>	YESx 1
	<b>CI</b>	YESx 1
	<b>RCA</b>	N/A

Other Features	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Norge, Dansk, Svenska, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	YES
	Wifi on Android	N/A
	Hotel Mode	YES
Power	Power Supply	DC12V-3A /AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	16W
	KWh/annum	24kWh
	Max power Consumption	36W
	Standby Power Consumption	<0. 5W
	Energy Efficiency Class	A
Accessories	USER'S Manual	N/A
	Remote Control	YES x 1
	Power Cable	N/A
	Adapter	YES x 1
	Adapter Cables	N/A
	Warranty	YES x 1
	Battery	1.5V(AAA)x2
Dimension	Unit Dimension With Stand (W x H x D mm)	463 x 160 x309
	Unit Dimension Without Stand (W x H x D mm)	463 x 48 x 280
	Weight of unit(kg)	3.2
	Gift Box Dimension(W x H x Dmm)	
	Weight of gift box with content(kg)	
	Weight of carton/paper(Kg)	
	Weight of styrofoam(Kg)	