


PO:SNCB14 17	Cello Electronics (UK) Ltd.	
	Product Photo	
General Feature	EAN	5060062267358
	Model No.	P50ANSMT-4K
	Panel(60Hz/120Hz/3D)	V500DJ2
	Destination Country	UK
	Safety and Regulation	CE
	Panel System	50 inch LED Panel(Approx. 127cm)
	Max. Resolution	3840 x 2160
	Contrast Ratio (Typical)	4000:1
	Brightness(TYP cd/m2)	200
	Display Colors	1.07G
	Viewing Angle(L/R/U/D)	CR≥10)89/89/89/89(CR≥10)89/89/89/89(CR≥10)89/
	HD Supported Definitions	3840x2160/1080p/1080i/720P/576P/480P
	AC Switch	N/A
	Cabinet Color	Silver
Wall Mounting Support(Screw Size)	400 x 400mm / M6 x 10	
Reception	TV Solution	Mstar3458
	TV System	DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz) DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz) DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz) DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz) DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	Number of channel for storing	400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	4 x 8W for Bass/2 x 8W for Treble
	Speaker Frequency range	155-18K Hz
	Speaker Distortion	<=5% Max
	Speaker Impedance	4 x 4ohm for Bass/2 x 8ohm for Treble
Connectors Jack	RF Antenna	1
	HDMI	YES x 3
	CVBS	YES x 1
	PC In	N/A
	Audio In	Audio x1
	Scart	N/A
	YPbPr	N/A
	Digital Audio out	YES× 1
	Earphone Out	N/A
	USB on TV	YES× 1
	CI	N/A
RCA	YES× 1	

	RJ45 on Android	YES× 1	
	Micro SD card on Android	YES× 1	
	USB on Android	YES× 2	
Android	SOC	M509280 PBM, ARM Cortex A7 quad core	
	RAM	1GB DDR3	
	GPU	6 core ARM Mali-450MP4	
	Built-in Flash	4GB	
	Wi-Fi	802.11 b/g/n	
	OS	Android 4.4.4	
Other Features	APS	DVBT, DVBC storage in capture order	
	OSD Language OSD Language OSD Language	English, Deutsch, Norge, Dansk, Svenska, Francais, Espanol, Portugese, Italian.	
	EPG (Electronic Program Guide)	7 days	
	Automatic Tuning	YES	
	Sleep Timer	YES(240min)	
	Color Temperature Adjustment	YES	
	Picture Mode	Standard / Dynamic / Mild / User	
	Home Mode	YES	
	Wifi on Android	YES	
	Hotel Mode	YES	
	Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
		Operation Power Consumption	85W
KWh/annum		120kWh	
Max power Consumption		120W	
Standby Power Consumption		<0.5W	
Energy Efficiency Class		A	
Accessories	USER'S Manual	N/A	
	Remote Control	YES x 1	
	Power Cable	YES x 1	
	Adapter	N/A	
	Adapter Cables	N/A	
	Warranty	YES x 1	
	Battery	1.5V(AAA)×2	
Dimension	Unit Dimension With Stand (W x H x D mm)	1106 x 286 x 765	
	Unit Dimension Without Stand (W x H x D mm)	1106 x 90 x 710	
	Weight of unit(kg)	12.75	
	Gift Box Dimension(W x H x Dmm)	1230x160x840	
	Weight of gift box with content(kg)	16.55	
	Weight of carton/paper(Kg)	3	
	Weight of styrofoam(Kg)	0.45	