

# GET FULLY EQUIPPED STORAGE DEALS



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A111 - 156 Pieces

- 6700SM - 1/4" SOCKETS HEX 4 - 13 MM  
4 - 4.5 - 5 - 5.5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 MM
- A6800DM-7 - 1/4" DEEP SOCKETS HEX 7 - 13 MM  
7-8-10-11-13MM
- 6956 - 1/4" SPINNER
- 6961 - 1/4" EXTENSION 100 MM
- 6966 - 1/4" UNIVERSAL JOINT
- 7800SM - 1/2" SOCKETS HEX 10 - 34 MM  
10-11-12-13-14-15-16-17-18-19-20-21-24-27-30-32-34 MM
- 7805DM - 1/2" SOCKETS DEEP 10 - 19 MM  
10-13-16-17-18-19 MM
- 7805SM - 1/2" SPARK PLUG 16 - 21 MM
- 8160-1/2 - 1/2" EXTENSION 125 MM
- 8162-1/2 - 1/2" EXTENSION 250 MM
- 8166-1/2 - 1/2" UNIVERSAL JOINT
- 8156-1/2 - 1/2" BREAKER BAR
- 7106S0080 - 1/2" sq 5/16" HEX BIT HOLDER
- 697 - 1/4" sq 1/4" HEX BIT HOLDER
- 70S - 5/16" BITS  
145 - 150 - 155
- 59/S100B - 100 PCS BIT SET RETAIL
- 6950SL - RATCHET 1/4" SLIM HEAD
- 8150SL - RATCHET 1/2" SLIM HEAD



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A112 - 24 Pieces

- S4RM/3T - RATCHET WRENCH DOUBLE FLAT
- 111M - COMBINATION WRENCH  
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27 MM
- 9070 - ADJUSTABLE WRENCH 9070 6"
- 9031 - ADJUSTABLE WRENCH 9031



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A115 - 10 Pieces

- 1-210-08-1-2 - BIN 1/2 ROUND, WITH HANDLE, CUT
- 9045-B-250 - BLACK SQUARE 250 MM
- 406T-225 - PLASTIC TORPEDO LEVEL 225
- MTB-5-25 - 5 M TAPE MEASURE 25 MM
- BFLA01 - Q3 LED TORCH
- K-AP-1 - GARDENER'S KNIFE
- 268 - MINI HACKSAW FRAMES
- 319-3906 - HACKSAW FRAME 319
- 5515T-52 - TELESCOPIIC MIRROR



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A114 - 22 Pieces

- 8224 IP - SLIP JOINT PLIERS 250 MM
- 2632 - COTTER PIN EXTRACTOR
- 3734 - COTTER PIN PUNCH  
2-3-4-5-6-8
- 2800-180 - CIRCLIP PLIERS 180 MM
- 2890-180 - CIRCLIP PLIERS 180 MM
- 2900-180 - CIRCLIP PLIERS 180 MM
- 2990-180 - CIRCLIP PLIERS 180 MM
- 4611-2 - NUT SPLITTER M16
- 479-24 - BALL PEIN HAMMER
- 1435/5 - STUD EXTRACTOR SET
- 1178-SCRIBE - SCRIBER CARB.TUNGSTEN
- 2101G-180IPS - SIDE CUTTER 180 MM
- 2430 G-160 IPRU - SNIPE NOSE CUTTING 160 IP



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A113 - 33 Pieces

- BE-9770 - SCREWDR SET HEX 1.5-10 BULK
- 808050 - RATCHETING BIT SCREWDRIVER
- BE-8150TB - ERGO™ THROUGH BLADE 1.0 x 5.5 x 100
- BE-8155TB - ERGO™ THROUGH BLADE 1.2 x 6.5 x 125
- BE-8256TB - ERGO™ THROUGH BLADE 1.6 x 8.0 x 150
- BE-8610TB - ERGO™ THROUGH BLADE PH1 x 100
- BE-8620TB - ERGO™ THROUGH BLADE PH2 x 100
- BE-8040 - SCREWDR ERGO™ 0.8 x 4.0 x 100
- BE-8150 - SCREWDR ERGO™ 1.0 x 5.5 x 100
- BE-8010S - SCREWDR ERGO™ IEC 0.4 x 2.5 x 75
- BE-8230S - SCREWDR ERGO™ IEC 0.6 x 3.5 x 100
- BE-8155 - SCREWDR ERGO™ 1.2 x 6.5 x 125
- BE-8800 - SCREWDR ERGO™ PZ0 x 60
- BE-8811 - SCREWDR ERGO™ PZ1 x 75
- BE-8821 - SCREWDR ERGO™ PZ2 x 100
- BE-8611 - SCREWDR ERGO™ PH1 x 75
- BE-8621 - SCREWDR ERGO™ PH2 x 100
- BE-8910 - SCREWDR ERGO™ TX 10 x 75
- BE-8915 - SCREWDR ERGO™ TX 15 x 100
- BE-8920 - SCREWDR ERGO™ TX 20 x 100
- BE-8925 - SCREWDR ERGO™ TX 25 x 125

## General Maintenance

**1470K6BKFF12SD**

### 245 piece tool trolley

- 26" 6 drawer Tool Trolley
- Heavy duty construction protects the drawers even if the body is damaged
- Swivel wheels for enhanced manoeuvrability
- Latch system prevents drawers opening while the unit is being moved

