

ideal for your application !



practical

top and bottom
grid patterned
cable gland plates

smart

easily dismantled
captive hinges

Standard
EN 50298
*

choice

all shape/type inserts,
numerous key locks

easy

easily removable glazed door,
linkages clip to parts in glass
reinforced polyamide,
single operator for 3 closure
points (on heights from 600 mm)

smart

clip-in front panel,
distance between rail and front panel
adjustable to all product sizes

and also...

strong

IK 08, body with double fold gutter,
chamfered vertical door edges, double
folded with safety glass.

watertight

IP 66, polyurethane seal and double
fold, 3 closure points from height
600 mm.

light and resistant

sheet steel door with cross structure,
corrosion resistant: plasma welded and
polyester paint finish.

attractive

chamfered vertical door edges,
plasma welded,
colour grey RAL 7032,
bonded safety glass.

accessories

enclosure can be equipped with Spacial
3D range accessories.

* Pending

Spacial 3D, your modular enclosure



durable

paint polyester with high UV resistance, treated hinges, aluminium hinge pins

simplified control

preassembled modular chassis, earthing collector included, enclosure is ready-to-use, packaging box reusable after wiring

choice

10 references depth 150 mm
from 24 to 240 modules
400 x 300 to 1000 x 600 mm

time saving

earthing connection mounted between body and door

