

3M Construction & Home Improvement Markets

Product Information Sheet



(Dec , 2002)

PRODUCT NAME: **Scotch® Transparent Duct Tape**

PRODUCT DESCRIPTION:

A transparent duct tape that is excellent for a variety of general household applications. Cannot be seen when applied, making your repair less obvious.

PRODUCT CONSTRUCTION:

Backing: Water resistant, transparent polyethylene coated, multi filament scrim
 Adhesive: Acrylic resin

AVERAGE PHYSICAL PROPERTIES:

		<u>ASTM TEST METHOD</u>
Adhesion to Steel:	34 oz./in. width	D-3330
Tensile Strength	24 lbs./in. width	D-3759
Elongation at Break	25 %	D-3759
Total Thickness	9 mils	D-3652
Maximum Temperature	173 deg. F	

AVAILABLE SIZES:

Catalog # 2120-A 1.88"x 20 yd. 48mmx 14.8 m

COLORS:

Transparent

APPLICATIONS:

- | | | |
|------------------------------|---------------|------------------------------|
| * Securing lightweight loads | * Bundling | * Temporary / general repair |
| * Sealing | * Reinforcing | * Splicing |

* Indoor/ Outdoor repairs

* Patching

* Packaging/box sealing

PRODUCT BENEFITS:

* Transparent

* Water resistant

* Durable

* UV resistant *

* Very Conformable

* Excellent tack

* Easy open packaging

* Wraps

* Tears easily

* Easy unwind

* Excellent adhesion

* Strong

- **The tape lasts six times longer than other all-purpose duct tapes based on accelerated weathering.**

“ Warning : Do not use on flues, chimneys, mufflers or tailpipes”

Page 2, Scotch® Transparent Duct Tape

STORAGE AND USE CONDITIONS:

To obtain best performance, use this product within one year from date of purchase and store under normal conditions of 70° F (21° C) and 50% relative humidity in the original carton.

FEATURES

Transparent polyethylene coated scrim backing

Acrylic resin adhesive

ADVANTAGES

* Resists moisture

* Conformable

* Hand tears easily

* Good tensile strength

* High tack

* Good Holding Power

BENEFITS

* Prolongs tape bond

* Easy application

* Excellent reinforcement

* Provides good seal

* UV Resistant

3M Construction and Home Improvement Markets Division
3M Center
Building 251-1C-09
St. Paul, MN 55144-1000

IMPORTANT NOTICE: All statements, technical information and recommendations herein are based on tests 3M believes to be reliable. 3M does not warrant or guarantee the accuracy or completeness of this information. User is responsible for determining whether this 3M product is fit for a particular purpose and suitable for user's method of application. Because there are many factors that can affect the use and performance of this product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate this product to determine whether it is fit for a particular purpose, is suitable for the user's method of application, and meets the user's performance specifications and expectations.

WARRANTY AND LIMITED REMEDY: This 3M product will be free from defects in material and manufacture for a period of one (1) year from the date of purchase. If this 3M product is defective within the warranty period stated above, your exclusive remedy and 3M's sole obligation shall be, at 3M's option, replacement of the 3M product or refund of the purchase price of the 3M product.

Limitation of Liability: 3M SHALL NOT BE LIABLE FOR ANY LOSS OR DAMAGES, WHETHER DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL (INCLUDING BUT NOT LIMITED TO LOST PROFITS, BUSINESS,

OR REVENUES) ARISING OUT OF THE USE OF OR INABILITY TO USE THIS 3M PRODUCT. No statement or recommendation not contained herein shall have any force or effect unless contained in an agreement signed by a 3M officer.