



JUNCTION BOX

i 12 SB-L



i 12 SB-L

Junction box

85 x 85 x 37 mm

Article number: 33271201

Junction box acc. to DIN EN 60670 (VDE 0606), 12 entries, 3 floor entries, complete with punching tool and blanking plug, with external fixing positions

red, without terminals, for VDE approved single terminals, for identifying circuits for safety lighting



Technical data

Measures

Width:	85 mm
Length:	85 mm
Height:	37 mm

Material:

Box:	polyethylene
Cover:	Polypropylene
material:	Polypropylene

Certificates



Accessory

HandyGrip VG 20 - Terminal strip

HandyGrip VG 21 - Terminal strip

HandyGrip VG 21 w - Terminal strip

HandyQuick SQ 32 - Screwless terminal

HandyQuick SQ 52 - Screwless terminal

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



JUNCTION BOX

i 12 SB-L

Other attributes

Color:	miscellaneous
Rated cross section:	2,5 mm ²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No