

# Tip Plug

## Insulated Standard: Small Handle (Solder or Crimp)

### SPECIFICATIONS

**Contact:** Brass per QQ-B-626D

**Finish:** Nickel


**Insulated Handle:** Nylon 6/6 per ASTM D4066

### RATINGS

**Current:** 10 amps

**Breakdown Voltage:** 3500 Vrms minimum †

**Contact Resistance:** 0.010 ohms maximum



NICKEL PLATING	
<b>SOLDER TYPE UP TO 16 GAUGE</b>	<b>CRIMP TYPE 16 GAUGE</b>
<b>PART NO.</b>	<b>COLOR</b>
105-0771-001	White

**For Standard Tip Jack: .080 (2.00) Diameter**

### FEATURES:

- Solder or crimp type connection
- Accepts wire sizes up to 16 gauge
- Nylon UL approved for self extinguishing

