



DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1864	C	Tolerance added	J.W.M.	3/14/08	JN	03/19/08	JN	03/19/08
1864	D	RoHS ADDED	DCM	1/24/06	JN	03/19/08	JN	03/19/08



Type No.	Tapped	"D"	"L"
2395	4-40	1/4	1/4 [6,35]
2396	4-40	1/4	3/8 [9,53]
2397	4-40	1/4	1/2 [12,70]
2398	4-40	1/4	5/8 [15,88]
2399	4-40	1/4	3/4 [19,05]
2400	4-40	1/4	7/8 [22,22]
2401	4-40	1/4	1 [25,40]
2402	6-32	1/4	1/4 [6,35]
2403	6-32	1/4	3/8 [9,53]
2404	6-32	1/4	1/2 [12,70]
2405	6-32	1/4	5/8 [15,88]
2406	6-32	1/4	3/4 [19,05]
2407	6-32	1/4	7/8 [22,22]
2408	6-32	1/4	1 [25,40]
2409	8-32	1/4	1/4 [6,35]
2410	8-32	1/4	3/8 [9,53]
2411	8-32	1/4	1/2 [12,70]
2412	8-32	1/4	5/8 [15,88]
2413	8-32	1/4	7/8 [22,22]
2414	8-32	1/4	1 [25,40]
3642	8-32	5/16	1 [25,40]
3641	1/4-20	1/2	1/4 [6,35]

NOTE: On threaded spacers 3/4" and longer, the tap is 3/8" from each end not through.

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	Jeff McVicker	9/24/97	Tapped Nylon Spacers			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	Jason Nash	03/19/08	A	TA-125	ta-125.dwg	D
	APPROVED BY:	DATE:	SCALE:	U.O.M.: INCHES [mm]	SHEET:	1 OF 1
	Jason Nash	03/19/08	NTS			

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.