



Connectors for mains connection

CA-series

HiPower

Type		Number of poles	Description	Order no.
 <p>CA 3 GD</p>		3 + PE	Panel-mounted socket Type of connection: screw Conductor cross-section: max. 1.5 mm ² Operating voltage: 250 V DC / 400 V AC Operating current: 10 A DC / 16 A AC	932 321-100
 <p>CA 6 GS</p>		6 + PE	Panel-mounted connector Type of connection: solder Conductor cross-section: max. 0.75 mm ² Operating voltage: 250 V AC/DC Operating current: 10 A AC/DC	932 326-100
 <p>CA 6 GD</p>		6 + PE	Panel-mounted socket Type of connection: solder Conductor cross-section: max. 0.75 mm ² Operating voltage: 250 V AC/DC Operating current: 10 A AC/DC	932 325-100
 <p>CA 00 SD 1</p>		-	Protection cap for all cable connectors with variable thread	831 530-400
 <p>CA 00 SD 3</p>		-	Protection cap for all cable sockets with variable thread	831 532-400