


Measuring leads



*System		Article type	Length "L" in cm	Technical Data	Order no. Colour
②	 	MVL 2/25	25 cm	0,5 mm ² , PVC 6 A, 17 mΩ	973 594-Colour** ● ●
		MVL 2/50	50 cm	0,5 mm ² , PVC 6 A, 26 mΩ	973 595-Colour** ● ●
		MVL 2/100	100 cm	0,5 mm ² , PVC 6 A, 44 mΩ	973 596-Colour** ● ●
⑥4	 	MKL 0,64/25-0,25	25 cm	0,25 mm ² , PVC 3 A	973 604-Colour** ● ●
⑥4	 	BNC - AL 0,64	120 cm	RG 58 A/U	933 844-001
④ ⑥4	 	MAL N 4-0,64/100-0,25	100 cm	0,25 mm ² , PVC 3 A	934 160-Colour** ● ●
	 	LMLH 50		30 plastic brackets	973 919-001

* System: ⑥4 = 0.64 mm system / ② ≙ 2 mm system / ④ ≙ 4 mm system / ● ≙ 4 mm safety system / ↔ ≙ 4 mm sliding sleeve system

** Colour: ● -100 ● -101 ● -102 ● -103 ● -104 ● -188