











*System Article type	Technical Data	Order no. Colour	Notes
(4)  PKI 110		max. 35 A 931 714-100 ● 931 714-101 ● 931 714-102 ● 931 714-103 ● 931 714-104 ● 931 714-188 ●	
(4)  PKI 100		max. 35 A 930 757-100 ● 930 757-101 ● 930 757-102 ● 930 757-103 ● 930 757-104 ● 930 757-188 ●	
●  SAB 2600 G M4		32 A surface-mounted socket, screw connection, M4 972 357-100 ● 972 357-101 ● 972 357-102 ● 972 357-103 ● 972 357-104 ● 972 357-188 ●	
●  BES 1000		Contact protection for screw-in and press-in sockets (SEB and SEP) 973 616-103 ●	

* System: (64) = 0.64 mm system / (2) ≙ 2 mm system / (4) ≙ 4 mm system / ● ≙ 4 mm safety system / ↔ ≙ 4 mm sliding sleeve system