

# EPIC® CONNECTORS


HA 3&4 Plugs & Receptacles

HA 3&4 Housings: Single Lever on Base




## SCREW TERMINATED INSERTS



HA 3





HA 4



All dimensions are in mm.




	Plug:	Receptacle:
HA 3	10.4200	10.4210
HA 4	10.4310	10.4320




Coding Pin: 10.4513

## HOODS

TOP ENTRY



SIDE ENTRY



All dimensions are in mm.

## TOP ENTRY HOODS

Material	Size of Entry			Without Cable Gland		With Cable Gland	
	PG	NPT	Metric	NPT Part #	Metric Part #	PG Part #	Metric Part #
Zinc Die Cast	11	1/2"	20	10.5121 NP	-	10.4265	19.4265
Black Plastic	11	1/2"	20	10.4255 NP	19.4255	10.4267	-
Grey Plastic	11	1/2"	20	10.4260 NP	19.4260	10.4264	-


# EPIC® CONNECTORS

HA 3&4 Housings: Single Lever on Base

## SIDE ENTRY HOODS

Material	Size of Entry			Without Cable Gland		With Cable Gland	
	PG	NPT	Metric	NPT	Metric	PG	Metric
				Part #	Part #	Part #	Part #
Zinc Die Cast	11	1/2"	20	10.5123 NP	-	10.4275	19.4275
Black Plastic	11	1/2"	20	10.4273 NP	19.4273	10.6206	-
Grey Plastic	11	1/2"	20	10.4270 NP	19.4720	10.4271	-

## PANEL MOUNT BASES




<b>Grey Metal</b>
10.4225


<b>Black Plastic</b>	<b>Grey Plastic</b>
10.4222	10.4220

All dimensions are in mm.

## ANGLED PANEL MOUNT BASES



All dimensions are in mm.



<b>Grey Metal</b>	<b>Black Plastic</b>	<b>Grey Plastic</b>
10.4235	10.4231	10.4230

## DUST COVERS WITH OR WITHOUT ATTACHMENT STRING



**Material:** Thermoplastic Resin or Aluminum      **Temperature:** -40°C to 125°C



Covers for Panel Mount or Surface Mount Bases/ and Cable Coupler Hoods	Part # with string	Part # without string
Dust Cover for HA 3/4 Housings with Male Insert	10.4304	10.4300
Metal Dust Cover for HA 3/4 Housings with Male Insert	10.5130	-
Dust Cover for HA 3/4 Housings with Female Insert (includes gasket)	10.4301	10.4303
Metal Dust Cover for HA 3/4 Housings with Female Insert (includes gasket)	10.5131	-

# EPIC® CONNECTORS


HA 3&4 Housings: Single Lever on Base

## SURFACE MOUNT BASES

### METAL



### PLASTIC




All dimensions are in mm.


Material	Size of Entry			Without Cable Gland		With Cable Gland	
	PG	NPT	Metric	NPT Part #	Metric Part #	PG Part #	Metric Part #
Zinc Die Cast	11	1/2"	20	10.5127 NP	-	10.4245	19.4245
Black Plastic	11	1/2"	20	10.5117 NP	19.5118	10.4247	-
Grey Plastic	11	1/2"	20	10.4240 NP	19.4241	10.4242	-

## CABLE COUPLER HOODS

### METAL



### PLASTIC



All dimensions are in mm.

Material	Size of Entry			Without Cable Gland		With Cable Gland	
	PG	NPT	Metric	NPT Part #	Metric Part #	PG Part #	Metric Part #
Zinc Die Cast	11	1/2"	20	10.5129 NP	19.5129	10.4295	19.4295
Black Plastic	11	1/2"	20	10.4292 NP	19.4292	10.6203	-
Grey Plastic	11	1/2"	20	10.4290 NP	19.4290	10.4291	-