



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

| REVISONS | | DOC. NO. | SPC-FO05 | Effective: | 12/21/98 | Doc No. | 880 | |
|----------|-----|-------------|----------|------------|----------|---------|--------|--------|
| DOP # | REV | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPRVD | DATE |
| 666 | A | RELEASED | HYO | 11/17/99 | JJC | 2/3/00 | DJC | 4/5/00 |



| APPROVALS | |
|-------------|----|
| USA | PA |
| Canada | 1 |
| Germany | 2 |
| Switzerland | 3 |
| Sweden | 4 |
| U.K. | 5 |
| Norway | 6 |
| Denmark | 7 |
| Finland | 8 |
| Italy | 9 |

Specifications:

1. Max. rating: 10A, 250V AC
2. Contact Resistance: < 10 milliohms
3. Insulation Resistance: > 10 Megohms
4. A.C. Breakdown: Pole 4.5 KV. Poles-Accessible Parts 6KV
5. Operating Temperature: -40° C to +70° C.
6. Withdrawal Force: 10N (Min.), 50N (Max.)
7. Female rewirable plug connectors straight cable entry.
8. Easily converts a power cord into a detachable power cordset.
9. Terminals: Screw.

Materials:

1. Molding: Nylon.
2. Flammability Rating: UL94V-0
3. Contacts: Brass, nickel plated.

DISCLAIMER
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

| | |
|--------------|----------|
| DRAWN BY: | DATE: |
| HISHAM ODISH | 11/17/99 |
| CHECKED BY: | DATE: |
| JOHN COLE | 2/3/00 |
| APPROVED BY: | DATE: |
| DANIEL CAREY | 4/5/00 |



SPC TECHNOLOGY

FEMALE REWIREABLE ASSEMBLY

| | | | | |
|----------------|------|---------------------|-----------------|--------|
| DRAWING TITLE: | SIZE | DWG. NO. | ELECTRONIC FILE | REV |
| | A | SPC4631 | 84N1432.DWG | A |
| SCALE: | NTS | U.O.M.: MILLIMETERS | SHEET: | 1 OF 1 |