

## Range box - AI-TWIN SORTI BOX BU - 3202986

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assortment box, supplied with TWIN ferrules according to DIN 46228-4, CSA-certified, box contains 50 pcs. AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

### Why buy this product

- Color coding and the transparent cover facilitate fast access to the required ferrules
- The practical assortment boxes are designed to keep your workshop tidy
- Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 947149
GTIN	4017918947149
Weight per Piece (excluding packing)	100.360 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### General

Color	blue
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	E-CU
Coating	tin-plated (galvanic)

#### Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	HB

#### Environmental Product Compliance

## Range box - AI-TWIN SORTI BOX BU - 3202986

### Technical data

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Articles in set

Ferrule - AI-TWIN 2X 0,5 - 8 WH - 3200933



Ferrule, sleeve length: 8 mm, length: 15 mm, color: white

Ferrule - AI-TWIN 2X 0,75- 8 GY - 3200807



Ferrules, for two 0.75 mm<sup>2</sup> conductors, sleeve length: 8 mm, with plastic collar, galvanically tin-plated, color: gray, color range according to NF C 63-023, CSA-certified

Ferrule - AI-TWIN 2X 1 - 8 RD - 3200810



Ferrule, sleeve length: 8 mm, length: 15 mm, color: red

Ferrule - AI-TWIN 2X 1,5 - 8 BK - 3200823



Ferrule, sleeve length: 8 mm, length: 16 mm, color: black

Ferrule - AI-TWIN 2X 2,5 -10 BU - 3200836



Ferrules, for two 2.5 mm<sup>2</sup> conductors, sleeve length: 10 mm, with plastic collar, galvanically tin-plated, color: blue, color range according to NF C 63-023, CSA-certified

# Range box - AI-TWIN SORTI BOX BU - 3202986

## Classifications

### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400218
eCl@ss 9.0	27400218

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000524
ETIM 6.0	EC000524

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121421

## Approvals

### Approvals

#### Approvals

CSA / CSAus / EAC / EAC / cCSAus





#### Ex Approvals

### Approval details

CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	247397
-----	---	---	--------

## Range box - AI-TWIN SORTI BOX BU - 3202986

### Approvals

CSAus		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	247397
EAC			EAC-Zulassung
EAC			7500651.22.01.00246
cCSAus		<a href="http://www.csagroup.org/us/en/services/testing-and-certification/certified-product-listing">http://www.csagroup.org/us/en/services/testing-and-certification/certified-product-listing</a>	