

3000 Series  
**VERSA SERIES**



FEATURED MODEL  
3050-V



FEATURED MODEL  
3210-V

**DIMENSIONS**

- POLYURETHANE SEAT**  
14" diameter  
2" seat thickness
- VINYL OR FABRIC SEAT**  
16" diameter  
Seat foam density:  
2 1/2lb, 55 IFD  
2 3/4" seat thickness

**UPHOLSTERY OPTIONS**

**STANDARD**



**ESD**



**CR & ESD/CR**



**BUILT TO ORDER**  
Each chair is configured to your exact specifications – upholstery, height range, base style, and glides/caster options.



Height Range	Base Style	Seat Height Adjustment	Seat Type	Standard Model #	ESD Model #	Cleanroom ISO4 Model #	Cleanroom ISO5 Model #	ESD/CR ISO5 Model #
DESK	23" Black Nylon	15" – 20"	Polyurethane	3000-P	-	-	-	-
		16" – 21"	Fabric	3000-F	-	-	-	-
		16" – 21"	Vinyl	3000-V	-	-	-	-
	25" Polished Aluminum	14 ½" – 19 ½"	Polyurethane	3050-P	-	3050C1-P	3050C2-V	3050E2-V
		15 ½" – 20 ½"	Fabric	3050-F	3050E-F	-	-	-
		15 ½" – 20 ½"	Vinyl	3050-V	3050E-V	-	-	-
MID	27" Black Nylon	18 ½" – 26"	Polyurethane	3300-P	-	-	-	-
		19 ½" – 27"	Fabric	3300-F	-	-	-	-
		19 ½" – 27"	Vinyl	3300-V	-	-	-	-
	27" Polished Aluminum	17 ½" – 25"	Polyurethane	3350-P	-	3350C1-P	3350C2-V	3350E2-V
		18 ½" – 26"	Fabric	3350-F	3350E-F	-	-	-
		18 ½" – 26"	Vinyl	3350-V	3350E-V	-	-	-
	22" Black Tubular Steel	18" – 23"	Polyurethane	3200-P	-	-	-	-
		19" – 24"	Fabric	3200-F	-	-	-	-
		19" – 24"	Vinyl	3200-V	-	-	-	-
	22" Chrome Tubular Steel	18" – 23"	Polyurethane	3210-P	-	3210C1-P	3210C2-V	3210E2-V
		19" – 24"	Fabric	3210-F	3210E-F	-	-	-
		19" – 24"	Vinyl	3210-V	3210E-V	-	-	-
TALL	27" Black Nylon	22" – 32"	Polyurethane	3500-P	-	-	-	-
		23" – 33"	Fabric	3500-F	-	-	-	-
		23" – 33"	Vinyl	3500-V	-	-	-	-
	27" Polished Aluminum	20 ½" – 30 ½"	Polyurethane	3550-P	-	3550C1-P	3550C2-V	3550E2-V
		21 ½" – 31 ½"	Fabric	3550-F	3550E-F	-	-	-
		21 ½" – 31 ½"	Vinyl	3550-V	3550E-V	-	-	-
	22" Black Tubular Steel	23" – 28"	Polyurethane	3600-P	-	-	-	-
		24" – 29"	Fabric	3600-F	-	-	-	-
		24" – 29"	Vinyl	3600-V	-	-	-	-
	22" Chrome Tubular Steel	23" – 28"	Polyurethane	3610-P	-	3610C1-P	3610C2-V	3610E2-V
24" – 29"		Fabric	3610-F	3610E-F	-	-	-	
24" – 29"		Vinyl	3610-V	3610E-V	-	-	-	



FEATURED MODEL  
3300-P

Updated 11/29/2016

## ACCESSORIES

### FOOTRING



STANDARD: ACF-18  
ESD: ACF-18E

Recommended for stools with a seat height range above 19".

### CASTERS

Casters add 1" to seat height range.



### HARD FLOOR CASTERS

Standard:  
5-star: 3850S/5  
Tubular: CADS/5  
ESD: CARD5S



### CARPET CASTERS

Standard:  
5-star: 3850/5  
Tubular: CAD/5  
ESD: CAPD5S



### SPECIALTY CASTERS

INTERVAL BRAKING  
Standard: IBCS  
ESD: IBCS-ESD

REVERSE BRAKING  
Standard: RBCS  
ESD: RBCS-ESD