

7000D Series
DURA SERIES



FEATURED MODEL
7301D

AVAILABLE COLORS



BLACK

DIMENSIONS

SEAT
19 ¼" W x 17 ¼" D
1 ½" Thick

BACK
15 ½" W x 14 ½" H
1" Thick

BUILT TO ORDER

Each chair is configured to your exact specifications – choice of arms, tilt, height range, base style, and glides/caster options.



Height Range	Base Style	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model #	Cleanroom ISO4 Model #	Cleanroom ISO5 Model #
DESK	23" Black Nylon	15" – 20"	2 Way	-	7000D	-	7000DC
			3 Way	-	7001D	-	7001DC
			4 Way	-	7002D	-	7002DC
	25" Polished Aluminum	14 ½" – 19 ½"	2 Way	-	7050D	7050DC	-
			3 Way	-	7051D	7051DC	-
			4 Way	-	7052D	7052DC	-
MID	27" Black Nylon	19" – 26 ½"	2 Way	20" Adj. Chrome	7300D	-	7300DC
			3 Way	20" Adj. Chrome	7301D	-	7301DC
			4 Way	20" Adj. Chrome	7302D	-	7302DC
	27" Polished Aluminum	18 ½" – 26"	2 Way	20" Adj. Chrome	7350D	7350DC	-
			3 Way	20" Adj. Chrome	7351D	7351DC	-
			4 Way	20" Adj. Chrome	7352D	7352DC	-
	22" Black Tubular Steel	19" – 24'	2 Way	19" Welded Chrome	7200D	-	-
			3 Way	19" Welded Chrome	7201D	-	-
			4 Way	19" Welded Chrome	7202D	-	-
	22" Chrome Tubular Steel	19" – 24'	2 Way	19" Welded Chrome	-	7210DC	-
			3 Way	19" Welded Chrome	-	7211DC	-
			4 Way	19" Welded Chrome	-	7212DC	-
TALL	27" Black Nylon	21" – 31"	2 Way	20" Adj. Chrome	7500D	-	7500DC
			3 Way	20" Adj. Chrome	7501D	-	7501DC
			4 Way	20" Adj. Chrome	7502D	-	7502DC
	27" Polished Aluminum	20 ½" – 30 ½"	2 Way	20" Adj. Chrome	7550D	7550DC	-
			3 Way	20" Adj. Chrome	7551D	7551DC	-
			4 Way	20" Adj. Chrome	7552D	7552DC	-
	22" Black Tubular Steel	24" – 29"	2 Way	19" Welded Chrome	7600D	-	-
			3 Way	19" Welded Chrome	7601D	-	-
			4 Way	19" Welded Chrome	7602D	-	-
	22" Chrome Tubular Steel	24" – 29'	2 Way	19" Welded Chrome	-	7610DC	-
			3 Way	19" Welded Chrome	-	7611DC	-
			4 Way	19" Welded Chrome	-	7612DC	-

FEATURED MODEL
7351D W/AA ARMS



ACCESSORIES

ARMS



AA

Standard and CR Models
Tilt models only, must be
ordered with chair.

CASTERS

Casters add
2" to seat
height range.



HEAVY DUTY 3" HARD FLOOR CASTERS

Standard: 3750S/5