

5000 Series - Standard, CR, ESD/CR  
8000 Series - ESD

# DORAL SERIES



### DIMENSIONS

**SEAT**  
18" W x 17 H  
2 3/4" Thick

**BACK**  
16" W x 10 H  
2" Thick

### UPHOLSTERY OPTIONS

#### STANDARD



#### ESD



#### CR & ESD/CR



### BUILT TO ORDER

Each chair is configured to your exact specifications – choice of upholstery, arms, tilt, height range, base style, and glides/caster options.



Height Range	Base Style	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model # Fabric	Standard Model # Vinyl	ESD Model #	Cleanroom ISO 5 Model #	ESD/CR ISO 5 Model #
DESK	23" Black Nylon	17" - 22"	2 Way	-	5000-F	5000-V	-	-	-
			3 Way	-	5001-F	5001-V	-	-	-
			4 Way	-	5002-F	5002-V	-	-	-
	25" Polished Aluminum	15 1/2" - 21"	2 Way	-	5050-F	5050-V	8050	5050C2	5050E2
			3 Way	-	5051-F	5051-V	8051	5051C2	5051E2
			4 Way	-	5052-F	5052-V	8052	5052C2	5052E2
MID	27" Black Nylon	20 1/2" - 28"	2 Way	18" Adj. Chrome	5300-F	5300-V	-	-	-
			3 Way	18" Adj. Chrome	5301-F	5301-V	-	-	-
			4 Way	18" Adj. Chrome	5302-F	5302-V	-	-	-
	27" Polished Aluminum	19" - 26 1/2"	2 Way	18" Adj. Chrome	5350-F	5350-V	8350	5350C2	5350E2
			3 Way	18" Adj. Chrome	5351-F	5351-V	8351	5351C2	5351E2
			4 Way	18" Adj. Chrome	5352-F	5352-V	8352	5352C2	5352E2
	22" Black Tubular Steel	20" - 25"	2 Way	19" Welded Chrome	5200-F	5200-V	-	-	-
			3 Way	19" Welded Chrome	5201-F	5201-V	-	-	-
			4 Way	19" Welded Chrome	5202-F	5202-V	-	-	-
	22" Chrome Tubular Steel	20" - 25"	2 Way	19" Welded Chrome	5210-F	5210-V	8210	5210C2	5210E2
			3 Way	19" Welded Chrome	5211-F	5211-V	8211	5211C2	5211E2
			4 Way	19" Welded Chrome	5212-F	5212-V	8212	5212C2	5212E2
TALL	27" Black Nylon	23" - 33"	2 Way	18" Adj. Chrome	5500-F	5500-V	-	-	-
			3 Way	18" Adj. Chrome	5501-F	5501-V	-	-	-
			4 Way	18" Adj. Chrome	5502-F	5502-V	-	-	-
	27" Polished Aluminum	21 1/2" - 31 1/2"	2 Way	18" Adj. Chrome	5550-F	5550-V	8550	5550C2	5550E2
			3 Way	18" Adj. Chrome	5551-F	5551-V	8551	5551C2	5551E2
			4 Way	18" Adj. Chrome	5552-F	5552-V	8552	5552C2	5552E2
	22" Black Tubular Steel	25" - 30"	2 Way	19" Welded Chrome	5600-F	5600-V	-	-	-
			3 Way	19" Welded Chrome	5601-F	5601-V	-	-	-
			4 Way	19" Welded Chrome	5602-F	5602-V	-	-	-
	22" Chrome Tubular Steel	25" - 30"	2 Way	19" Welded Chrome	5610-F	5610-V	8610	5610C2	5610E2
			3 Way	19" Welded Chrome	5611-F	5611-V	8611	5611C2	5611E2
			4 Way	19" Welded Chrome	5612-F	5612-V	8612	5612C2	5612E2

## ACCESSORIES

### BACK UPGRADE

Medium Back: (MDB)



### ARMS



A5  
Standard Models



A8  
ESD Models

### CASTERS

Casters add 1" to seat height range.



### HARD FLOOR CASTERS

Standard:  
5-star: 3850S/5  
Tubular: CADS/5  
ESD: CARD5S



### CARPET CASTERS

Standard:  
5-star: 3850/5  
Tubular: CAD/5  
ESD: CAPD5S



### SPECIALTY CASTERS

**INTERVAL BRAKING**  
Standard: IBCS  
ESD: IBCS-ESD

**REVERSE BRAKING**  
Standard: RBCS  
ESD: RBCS-ESD