

# LabelManager™ Wireless PnP



## Wireless Plug and Play Label Maker for PC or Mac®

- Share with others in your wireless network — easy set-up
- No software to install – plug and play functionality for immediate out-of-box use\*
- Customize labels with any fonts or graphics on your computer through the PC or Mac®\*\* connection
- Print crystal-clear graphics, barcodes, and logos at 300 dpi resolution
- Make multi-label printing easier with automatic label cutter
- Stores multiple individual and enterprise Wi-Fi networks for automatic recognition
- Battery pack recharges via USB connection - no AA batteries needed
- Prints barcodes: QR Codes, UPC-A, UPC E, Code 39, Code 39 Library, Code 128, EAN 8, EAN 13, Codabar, Codabar Library, UCC/EAN 128, ITF-14



\* When USB is plugged into the computer

\*\* Compatible with Windows Vista®, Windows® 7, Windows® 8, Mac OS® X 10.5 or later - Intel® only

### Single Unit Includes:

- LabelManager Wireless PnP Label Maker
- D1 Starter Label Cassette, Black on White, 24mm x 3m
- Rechargeable Battery Pack
- USB Power Adapter
- Quick Start Card and Quick Reference Guide
- 2-Year Limited Warranty Card



### Quick Specs

Unit Dimensions (H x W x L)	56.5 x 144 x 162 mm
Weight (excluding battery)	555 g
Mac®/PC Compatible	Yes
Accepts Label Sizes	6, 9, 12, 19, 24mm
Tape Platform	D1, IND
Resolution	300 dpi
Printing System	Thermal Transfer
Print Speed	15mm/sec
Barcodes	Yes
Cutter Type	Automatic
Batteries	Rechargeable
Adapter	Yes, USB Power Adapter
Networking	Wireless 802.11bgn networks
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price	
S0969000	LabelManager Wireless PnP FR/DE/NL	Unit	10.0	18.7	25.0	1.13	1	3501170969007		
		Shelf	-	-	-	-	-	-	-	
		Case	39.0	26.5	32.0	7.47	6	-	-	
		Pallet	120.0	80.0	111.0	204.28	144	-	-	
<b>Accessories</b>										
1881983	USB Cable & Adapter Bundle	Unit	11.501	18.99	8.99	0.142		3501178819830		



## D1 Standard\*

For hundreds of tasks around the office or home office, such as filing, storage and asset management.

Temperature rating: -18°C to 90°C

\*For use with LabelManager™ series and LabelWriter™ 450 Duo

D1 Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
<b>D1 STANDARD</b>													
6mm	7m	S0720780	S0720770	S0720790	-	-	-	-	-	-	-	-	-
9mm	7m	S0720680	S0720670	S0720730	S0720710	S0720740	S0720720	-	-	S0720690	-	S0720700	-
12mm	7m	S0720530	S0720500	S0720580	S0720560	S0720590	S0720570	S0720600	S0720610	S0720540	S0720510	S0720550	S0720520
19mm	7m	S0720830	S0720820	S0720880	S0720860	S0720890	S0720870	S0720900	S0720910	S0720840	-	S0720850	-
24mm	7m	S0720930	S0720920	S0720980	S0720960	S0720990	S0720970	S0721000	S0721010	S0720940	-	S0720950	-



## IND Vinyl\*

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

## IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 150°C

## IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

For use with LabelManager™ series and LabelWriter™ 450 Duo and Rhino™ series  
\*Only compatible with Rhino™ labeling tools

IND Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
<b>IND VINYL</b>													
9mm	5.5 m	18443	-	-	-	-	-	-	1805437	-	-	-	-
12mm	5.5 m	18444	-	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412	-
19mm	5.5 m	18445	-	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418	-
24mm	5.5 m	1805430	-	1805431	1805427	1805425	1805429	1805432	1805426	1805423	1805428	1805424	-
<b>IND PERMANENT POLYESTER</b>													
6mm	5.5 m	1805442	1805440	-	-	1805441	-	-	-	-	-	-	-
9mm	5.5 m	18482	18508DMO	-	-	18485	-	-	-	-	-	-	-
12mm	5.5 m	18483	622289	-	-	18486	-	-	-	-	-	-	-
19mm	5.5 m	18484	622290	-	-	18487	-	-	-	-	-	-	-
24mm	5.5 m	1734523	1805433	-	-	1805434	-	-	-	-	-	-	-
<b>IND FLEXIBLE NYLON</b>													
12mm	3.5 m	18488	-	18490	-	-	-	-	-	-	-	-	-
19mm	3.5 m	18489	-	18491	-	-	-	-	-	-	-	-	-
24mm	3.5 m	1734524	-	1734525	-	-	-	-	-	-	-	-	-

Country of Origin: Belgium

**DISTRIBUTED BY:**  
Newell Europe Sàrl  
Chemin de Blandonnet 10  
1214 Vernier – Switzerland  
WWW.DYMO.COM



A Newell Rubbermaid Brand

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

©2014 Newell Europe LLC