



VISIO-TEK™

Wireless digital microscope

THE PORTABLE
DIGITAL MICROSCOPE
WITH INTEGRATED WI-FI

VISIO-SCOPE: Kit of VISIO-EYE Wi-Fi camera, VISIO-L04 Lens & Adapters and 3 Spacer Rings

VISIO-SCOPE is a complete solution with a digital C-Mount Wi-Fi camera (VISIO-EYE) that allows you to wirelessly digitalize any traditional optical device in seconds.

Visio-scope is compatible with all optical microscopes. Digitalize images and take measurements and photos from your standard optical device using your tablet, smartphone or PC with dedicated Apps and Software. The images can be displayed on different devices simultaneously.



FEATURES

- Photo & video resolution: 1.3MPx - 1280x1024, 640x480, 320x240
- Frame rate: up to 30fps
- IEEE 802.11 b/g/n standards compliant
- Wireless transmission distance: up to 5m
- Frequency range: 2.400GHz ~ 2.4835GHz
- Li-ion battery: continuous working time - appx. 2 hours
full charging time - appx. 2 hours
- Camera sensor: CMOS 1/4"
- Lens: high definition microscopy lens
- Dimension: 36mm (Ø) x 75mm (length)
- PC interface: USB 2.0
- Mini USB cable: 1.2m
- Power consumption: max 2.5W

APPLICATIONS

- *Industrial and Electronic Inspection/QC*
- *Education*
- *Research and Scientific Analysis*
- *Forensics*
- *Print inspection*
- *Textile inspection*
- *Trichology*
- *Entomology*
- *Botany*
- *Mineralogy*
- *Collectibles*
- *Jewelry and Watch Repair*
- *Reading assistance*
- *And more ...*



www.visio-tek.net For more information: info@visio-tek.net

TECHNICAL DATA SHEET