

DCP Temperature Controller



— **Features:**

- Temperature sensitive speed control
- Choice of pre-set profiles
- Alarm output for fan failure, over-temperature, sensor failure
- Consumes <1mA
- Rugged over-moulded construction
- Supplied with NTC Temperature sensor lead (2m)

Part Number	Supply Voltage VDC	Temperature Profile °C	Ambient Temperature °C	Max Humidity % RH	Width mm	Height mm	Depth mm
CPCXX2040SC-F	10-57	20-40	-30 - +70	90	45	56.5	8
CPCXX3555SC-F	10-57	35-55	-30 - +70	90	45	56.5	8

