

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151340406](#)
Status: **Active**
Overview: [PicoBlade Connector System](#)
Description: PicoBlade-to-PicoBlade Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, 4 Circuits, Natural

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-----------------------------|--|
| Product Family | Cable Assemblies |
| Series | 15134 |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | PicoBlade-to-PicoBlade |
| Overview | PicoBlade Connector System |
| Product Literature Order No | 987651-6143 |
| Product Name | PicoBlade OTS |
| UPC | 889056870887 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 600.00mm |
| Circuits (Loaded) | 4 |
| Color - Resin | Natural |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Polyester |
| Net Weight | 4.000/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.25mm |
| Plating min - Mating | 0.889µm |
| Plating min - Termination | 0.914µm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 0.90mm |
| Wire Size AWG | 28 |
| Wire/Cable Type | UL 1061 |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 125V |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2012341356-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

| | |
|-----------------|---------------|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

[15134 Series](#)

Mates With

PicoBlade Header [53261](#) , [53047](#) , [53398](#) ,
[53048](#)