



Main

Range of product	Altivar
Range compatibility	Altivar Machine ATV340 Altivar Process ATV900 Altivar Process ATV600
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To save and download configurations To display the current values To control, adjust and configure the drive
IP degree of protection	IP65

Complementary

Language	Greek Korean Italian Polish Finnish Estonian Danish Dutch Bulgarian Chinese Brazilian Spanish Portuguese Czech English Taiwanese Swedish Turkish Slovak Lituanien Hungarian Norwegian
----------	--

French
Russian
German
Romanian

Realtime clock	Built-in
Battery size	CR2032
Battery life	10 yr
Display type	Backlit LCD screen white and red
Messages display capacity	8 lines
Pixel resolution	240 x 160
Product weight	0.2 kg

Environment

Ambient air temperature for operation	> -15...50 °C
---------------------------------------	---------------

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity