

## Luminaire Terminal block

This 3 pole push-wire luminaries connector is capable of taking 2 conductors per pole. The connector poles are marked for L, N and E and conductor release is via the lever action (rear terminal) or through screwdriver insertion (front terminals). Mounting is via snap-in feet moulded into the base of the product which is also supplied complete with a detachable tool-less cable strain relief and earth foot.

### Features & Benefits:

- Complies with IEC/EN60998-2-2
- Push-wire "Quick-Connection"
- Easy mounting via fixing 'snap-in' feet.
- Supplied complete with detachable tool-less strain relief & earth foot.



### Specification:-

Part Number: -	HYLC-03KIT
Housing	Polyamide 66
Metal Part	Plated Brass / Steel spring
Voltage (V)	450
Ampere (A)	10

Wiring Capacity (mm <sup>2</sup> )	Wiring Holes (a) + (b)	Wiring Hole (c)
Installation / User-side(with press-release button)	0.5-2.5	0.5-0.75
Factory / Internal - side	0.5-1.5	0.5-0.75
(without press-release button)	solid only	solid only