


## IMPSTAR 40

### 40W LED Beam Moving Head with Halo Ring



A compact but powerful moving head beam light with colour changing/chasing halo ring effect. This mini moving beam is smooth in operation and with its 8 degree beam angle makes a dramatic impact in any light show. The controllable 4 section halo ring produces a visual and mesmerising experience of colour changes and chase effects making the Impstar40 suitable for bars, clubs, mobile DJs and stage use.

- Beam light source: 40W 4-in-1 Quad-colour LED (RGBW)
- Halo light source: 12x 5050SMD Tri-colour LEDs (3 per segment)
- Beam angle: 8°
- DMX channels: 16 or 21 selectable
- Operating modes: Auto, Show, Sound active, Master/slave and DMX
- 4 Pre-programmed shows
- 4 Auto programs with adjustable speed
- Built-in microphone with adjustable sensitivity for sound active mode
- Dimming: 0-100%
- Strobe flash rate: 1-25 flashes per second
- Pan: 540°, Tilt: 210°
- Pan & Tilt inverse modes
- 4 Button menu system with LED display
- Fan cooled
- Supplied with mounting bracket for use with couplers
- 3 Pin XLR DMX in/out
- IEC power in
- Power consumption: 60W
- Power supply: 90-240V AC, 50/60Hz
- Dimensions (WxHxD): 175x250x145mm
- Weight: 2.8kg