



# 8+ Way Signal Booster 27824HSR



Filtering



Auto Line Powering



Output

27824HSR

## 8+ Way Signal Booster

Distributes TV/FM/DAB signal for 8 TVs & high level output for further distribution

### Features & Benefits

- Distributes HD TV, DAB and FM signals
- 2 Inputs - 1x TV signal and 1x DAB/FM
- 8 Outputs + FULL output - suitable for 8 or more TVs/radios
- 11dB Gain ideal for long cable runs or weak signals
- 45dB 4G interference protection
- RED Compliant - updated to improve signal handling
- Auto Line powering for masthead amplifiers



### Technical Specification:

Booster	In	Out	Frequency VHF Signal UHF Signal	Suitable for	Max Gain	Full Output Port	Noise	Isolation Out/Out	Max Output	Typ. 4G Protection
27824HSR SLx8+1	2	8	87-230MHz 470-782MHz	FM/DAB/ TV Ch 21-59 Freeview	11dB	18dB	<3dB	20dB	90dBµV	>45dB

Distributed By:

