

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

### Complementary

Line Rated Current	150 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	10 kA 240 V AC
[Ics] rated service short-circuit breaking capacity	50 %
Breaking capacity code	B
Mounting mode	I-Line
Electrical connection	Lugs on load: AWG 4...300 kcmil (aluminium/copper) I-Line connection on line AC connection
Phase connection	AC
Magnetic hold current	1200 A
Magnetic tripping current	2400 A

### Environment

Product certifications	IEC UL listed CSA
------------------------	-------------------------

### Ordering and shipping details

Category	01023 - Q2 BREAKER & SWITCH
----------	-----------------------------

Discount Schedule	DE2
GTIN	00785901403814
Nbr. of units in pkg.	1
Package weight(Lbs)	4.71
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------