

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Motor Circuit Protector
Range of product	GJL
Magnetic tripping current	90...330 A
Line Rated Current	30 A
Product certifications	CSA UL recognized
System Voltage	600Y/347 V AC
Mounting mode	Unit mount
Poles description	3P
Electrical connection	Lugs
AWG gauge	AWG 8...AWG 1/0 (aluminium) AWG 14...AWG 1/0 (copper)

Ordering and shipping details

Category	00924 - GJL THERM-MAG AND MAG-GARD
Discount Schedule	DE2
GTIN	00785901793618
Nbr. of units in pkg.	1
Package weight(Lbs)	2.21
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
