

# Product data sheet

## Characteristics

# QBM32200TN

PowerPact Q - molded case circuit breaker - 3-pole - 10 kA - 208Y/120 V - 200 A

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

### Complementary

Line Rated Current	200 A
System Voltage	208Y/120 V AC
Number of poles	3
Breaking capacity	10 kA 240 V AC
[Ics] rated service short-circuit breaking capacity	50 %
Breaking capacity code	B
Mounting mode	Unit mount
Electrical connection	Lugs on line: AWG 4...300 kcmil (aluminium/copper) Terminal nut on load
Magnetic hold current	1200 A
Magnetic tripping current	2400 A

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

### Ordering and shipping details

Category	00187 - Q2M REPL MAIN CB
Discount Schedule	DE2A

GTIN	00785901662679
Nbr. of units in pkg.	1
Package weight(Lbs)	4.6299999999999999
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------