

# Product data sheet

## Characteristics

# QDL22225

PowerPact Q - molded case circuit breaker - 2-pole - 25 kA - 240 V - 225 A

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

### Complementary

Line Rated Current	225 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	25 kA 240 V AC
[Ics] rated service short-circuit breaking capacity	50 %
Breaking capacity code	D
Mounting mode	Unit mount
Electrical connection	Lugs on load: AWG 4...300 kcmil (aluminium/copper) Lugs on line: AWG 4...300 kcmil (aluminium/copper)
Magnetic hold current	1200 A
Magnetic tripping current	2400 A

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

### Ordering and shipping details

Category	00005 - QO,Q2L 2P ENCL & BREAKERS
Discount Schedule	DE2A

GTIN	00785901702894
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3200000000000003
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------