

Product data sheet

Characteristics

QBM22150TN

PowerPact Q - molded case circuit breaker - 2-pole - 10 kA - 240 V - 150 A

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|---------------------------|------------------|
| Product or component type | Circuit breaker |
| Range of product | PowerPact Q |
| Trip unit technology | Thermal-magnetic |

Complementary

| | |
|---|--|
| Line Rated Current | 150 A |
| System Voltage | 240 V AC |
| Number of poles | 2 |
| Breaking capacity | 10 kA 240 V AC |
| [Ics] rated service short-circuit breaking capacity | 50 % |
| Breaking capacity code | B |
| Mounting mode | Unit mount |
| Electrical connection | Lugs on line: AWG 4...300 kcmil (aluminium/copper) Terminal nut on load |
| Magnetic hold current | 1200 A |
| Magnetic tripping current | 2400 A |

Environment

| | |
|------------------------|-------------------------|
| Product certifications | IEC UL listed CSA |
|------------------------|-------------------------|

Ordering and shipping details

| | |
|-------------------|--------------------------|
| Category | 00187 - Q2M REPL MAIN CB |
| Discount Schedule | DE2A |

| | |
|-----------------------|----------------|
| GTIN | 00785901417873 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 3.27 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1413 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|