



## RDLP-815D

### ► SINGLE-ENDED CORDSETS



CDS LP 8 M ST 4.6 ZSM8X22 1 NP B 4.57 63.5 12.7  
6.00 N

Part Number: 80792

### SPECIFICATIONS

Number of Contacts	8
Number of Connectors	1
Cable Jacket Material	PVC
Cable Jacket Color	Yellow
Connector Body Material/Color	PUR Black
Outside Cable Diameter (mm)	6
Cordset Length (m)	4.57
Trunk Length (m)	No Trunk
Shield/No Shield	No Shield
Coupling Material/Color	Nylon Black
Maximum Temp. (°C)	55
IP Rating	IP67

<b>Primary Connector Type</b>	LP-Custom
<b>Primary Coupling Method</b>	LP-Custom
<b>Primary Gender</b>	Male
<b>Primary Orientation</b>	Straight
<b>Primary Number of Conductors</b>	8
<b>Primary AWG</b>	22
<b>Secondary Connector Type</b>	Flying Leads
<b>Feature: Hazardous Area</b>	No
<b>Feature: Chemical Resistant</b>	No
<b>Oil/Grease Resistant</b>	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America