



K50BCLR2A120Q-39906

▶ PRODUCTS FOR INDUSTRIAL AUTOMATION



K50 Beacon EZ-LIGHT: 1-Color Perimeter & Top View

Mode: Flash Only 1.6Hz Voltage: 85-130 V ac

Housing: Polycarbonate IP69K Colors: Red

Micro 3-pin Quick Disconnect

Part Number: 39906

SPECIFICATIONS

Housing Style	Base Mount - Dome Window
Primary Housing Material	Polycarbonate
Indication	Yes
Mounting Thread	30 mm
Color Option 1/Job Light	Red
Current - Color (mA)	60
Connection Type	Integral QD
Number of Pins/Conductors	3
Supply Voltage	85-130 V ac
Max Input Response Time (ms)	1
Size/Length (mm)	50
Environmental Rating	IP69K

Max Op. Relative Humidity Non-Condensing (%)	95% @ 50°C
Max Op. Temperature (°C)	50
Min Op. Temperature (°C)	-40
Primary Window Material	Polycarbonate
Vibration and Mechanical Shock	Meets Mil. Std. 202F requirements method 201A. Also meets IEC 947-5-2; 30G 11 ms duration, half sine wave.
Feature: Washdown Rated	Yes
Feature: Audible	No
Feature: Chemical Resistant	No
Modbus RTU	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America