

<b>DATA SHEET</b>	44423225
<b>EPIC® MHB 17 CM</b>	Valid from: 22.02.2017

## Description

- Universal module for 17 contacts in smallest space
- Crimp connection for permanent vibration-proof contact
- EPIC® MH system is mateable with the market standard
- The mix of different functions is one plug guarantees high flexibility



## General characteristics

Contact type	socket
Number of contacts	17
Mating cycles	500
Material	Polyamide, glass fibre-reinforced
Inflammability class acc. with UL 94	V0
Pollution degree	3
Temperature range	-40° C to +125° C
Termination methods	crimp termination: 0.14 – 2.50 mm <sup>2</sup> Epic® MH 6 multi-frame Epic® MH 10 multi-frame Epic® MH 16 multi-frame Epic® MH 24 multi-frame
Suitable frame	
Suitable contacts	Epic® H-D 1.6 machined contacts

## Electrical characteristics

Rated voltage	160 V
Contact resistance	< 5 mΩ
Rated impuls voltage	2.5 kV
Rated current	10 A


## Standards/Approvals

Fire protection on railway vehicles	according EN 45545-2 requirement sets R22 and R23 hazard level HL1, HL2 and HL3
-------------------------------------	---



<b>DATA SHEET</b>	44423225
<b>EPIC® MHB 17 CM</b>	Valid from: 22.02.2017

**Drawings**



**Note**

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB44423225EN Version: 00	Page 2 of 2
---	---------------------------------------	-------------

We reserve all rights according to DIN ISO 16016.