

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210502011](#)
Status: **Active**
Overview: mPm® DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C, 2 Pole Plus Ground, to 5.0m (16.40') PVC Cable Pigtail, Yellow LED, Black Nitrile Gasket, 24V

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	121050
Connector End A	Brad mPm DIN C
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mPm® DIN Valve Connectors
Product Name	mPm
Protocol	N/A
Region	America, Europe
Type	Single Ended
UPC	883906587673

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yes
Material - Cable Jacket	PVC
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Gold over Nickel
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	20
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	24V AC/DC

Material Info

Engineering Number	E492B2A50011C4H
--------------------	-----------------

Reference - Drawing Numbers

Sales Drawing	SD-121050-002
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121050 Series](#)