

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200700237](#)  
**Status:** **Active**  
**Description:** MIC 5P M/MF BULKHEAD FEED-THRU

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">120070</a>
Approvals	N/A
IP Rating	IP68
Material - Contact	Brass
Product Name	Micro-Change (M12), Nano-Change (M8)
Type	In-Line Interconnect
UPC	78678845499

**Physical**

Cable Diameter	4.10 - 8.10mm (.161-.319")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male-Female
Keyway	Single
Material - Connector Body	N/A
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	n/a
Net Weight	45.250/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

**Material Info**

Engineering Number	8R5L30
--------------------	--------

**Reference - Drawing Numbers**

Sales Drawing	SD-120070-018
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[120070 Series](#)