



JUNCTION BOX

Q 12-2,5<sup>2</sup>



Q 12-2,5<sup>2</sup>

Junction box

85 x 85 x 37 mm

Article number: 33441201

Junction box acc. to DIN EN 60670 (VDE 0606), 12 entries, with conductor retention acc. to VDE 0606 for NYM 5 x 2.5 mm<sup>2</sup>, 7 of which are accessible from the top, 3 floor entries, with external fixing positions

Grey, with 5 interlockable screw terminals 2.5 mm<sup>2</sup>



Technical data

Measures

Width:	85 mm
Length:	85 mm
Height:	37 mm

Material:

Box:	Polypropylene
Cover:	Polypropylene
material:	Polypropylene

Certificates



Accessory

HandyGrip VG 20 - Terminal strip

HandyGrip VG 21 - Terminal strip

HandyGrip VG 21 w - Terminal strip

HandyQuick SQ 32 - Screwless terminal

HandyQuick SQ 52 - Screwless terminal

Environmental attributes

Ambient temperature (24 h):	35 °C
Ambient temperature (max.):	40 °C
Ambient temperature (min.):	-25 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



JUNCTION BOX

# Q 12-2,5<sup>2</sup>

## Other attributes

Color:	Grey
Rated cross section:	2,5 mm <sup>2</sup>
Rated insulation voltage AC:	400 V
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP20 - acc. EN 60529 / DIN VDE 0470-1
weatherproof:	No
Equipment:	Terminal