



JUNCTION BOX

2K-16 AB-2,5²/w

2K-16 AB-2,5²/w

Junction box

130 x 85 x 37 mm

Article number: 34811601

Junction box acc. to DIN EN 60670 (VDE 0606), 16 entries, 3 floor entries, with self-sealing, soft inlet membranes, tools not required for opening the cable entry, seal range 2 - 14 mm, with external fixing positions

White, with screw terminal 5-pole - 2.5 mm²



Technical data

Measures

Width:	130 mm
Length:	85 mm
Height:	37 mm

Material:

Box:	polypropylene, membrane out of TPE
Cover:	Polypropylen, Copolymer
material:	Polypropylene

Certificates



Accessory

ZEL 2K-12 - Strain relief

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



JUNCTION BOX

2K-16 AB-2,5²/w

Other attributes

Rated cross section:	2,5 mm ²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Entries:	19
Ingress protection:	IP55 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No
Equipment:	Terminal
Color:	white